



WHY ACC

- ü ACC offers products from the **top-class** activated carbon manufacturers.
- ü ACC ensures a **one-stop service** for varies demands from customers.
- ü **Double quality guarantee** from both manufacturer side and ACC side after production and before delivery.
- ü Approved by many authorized institutions from different fields such as **NSF, BV, HALA, Kosher**.etc.

ACC SolRe for Solvent Recovery

It has a strong separation and recycling performance for ethers, ketone, alcohol, tetrahydrofuran, dichloromethane, trichloromethane, trichloroethylene, perchlorovinyl, carbon disulfide, benzene, toluene, formyl, gasoline, ethyl acetate, fluorinated hydrocarbons and other organic solvent and organic vapors.

Features & Benefits

- I High benzene adsorption
- I Good Hardness
- I Advanced pore structure

Item No.	Specification							
SR ZH	Moisture (%)	Hardness (%)	Ash (%)	CTC (%)	Benzene Adsorption (%)	Apparent Density (g/l)	Fire Point (°C)	Size (mm)
2080B	≤5	≥95	≤12	≥80	≥44	460±20	>400	2.0±0.2
2090B	≤5	≥93	≤12	≥90	≥50	430±20	>400	2.0±0.2
20100B	≤5	≥90	≤14	≥100	≥55	390±20	>400	2.0±0.2
20110B	≤5	≥90	≤16	≥110	≥60	350±20	>400	2.0±0.2
3080B	≤5	≥95	≤12	≥80	≥44	450±20	>400	3.0±0.2
3090B	≤5	≥93	≤12	≥90	≥50	410±20	>400	3.0±0.2
30100B	≤5	≥90	≤14	≥100	≥55	380±20	>400	3.0±0.2
4080B	≤5	≥95	≤12	≥80	≥44	440±20	>400	4.0±0.2
4090B	≤5	≥93	≤12	≥90	≥50	410±20	>400	4.0±0.2
40100B	≤5	≥90	≤14	≥100	≥55	380±20	>400	4.0±0.2
40110B	≤5	≥90	≤16	≥110	≥60	350±20	>400	4.0±0.2
5070B	≤5	≥95	≤12	≥70	≥38	460±20	>400	5.0±0.2
6070B	≤5	≥90	≤12	≥70	≥33	450±20	>400	6.0±0.2
7070B	≤5	≥90	≤12	≥70	≥38	440±20	>400	7.0±0.2

Package: Packed in 500kg jumbo bag. Other packaging is available upon your request.

Standards: All the above test methods are performed using ASTM protocol for activated carbon.

Xiamen All Carbon Corporation

TEL: +86 592 2278129 FAX: +86 592 2278123

E-MAIL: info@allcarbon.com.cn [Http://www.allcarbon.com.cn](http://www.allcarbon.com.cn)

Add: Unit F-G 10/F, Zhenhaoge Building, Guomao Golden Coast, No.99 Lujiang Road. Xiamen China 361001