



ACC GS PK Series for Gas Separation

WHY ACC

- ✓ ACC offers products from the **top-class** activated carbon manufacturers.
- ✓ ACC ensures a **one-stop service** for varies demands from customers.
- ✓ **Double quality guarantee** from both manufacturer side and ACC side after production and before delivery.
- ✓ Approved by many authorized institutions from different fields such as **NSF, BV, HALA, Kosher**.etc.

These series products are used in separating nitrogen and carbon dioxide from the air in separating methane from ferment gas, and in separating hydrogen from blast furnace gas or from the methanol gas.

SPECIFICATIONS		
Item No.	PK-3060 A	PK-1560 A
Moisture %	2 max	2 max
Hardness %	96 min	90 min
Ash %	10 max	10 max
Iodine number m/g	1010 min	1010 min
CTC %	60 min	60 min
Apparent density g/L	490 – 530	490 – 530
Particle size mm	3.0	3.0

Package: Packed in big jumbo bags or 25kg bags. Other packaging is available upon your request.

Standards: All the above test methods are performed using ASTM protocol for activated carbon.