



ACC WS A for Water Treatment

WHY ACC

- ✓ ACC offers products from the **top-class** activated carbon manufacturers.
- ✓ ACC ensures a **one-stop service** for varies demands from customers.
- ✓ **Double quality guarantee** from both manufacturer side and ACC side after production and before delivery.
- ✓ Approved by many authorized institutions from different fields such as NSF, BV, HALA, Kosher.etc.

These series products are used for dechlorination, deoiling of industrial water such as food, chemical industry, electric power, electric plate, etc, and further purifying treatment of potable water and sewage water.

Features

- High adsorption capacity
- Low ash content

SPECIFICATIONS

WS A

Item No.	ZJ30	ZJ25	ZJ15	PJ20	PJ 8x16	PJ 8x30	PJ 12x40	BG 4x8	BG 8x30	BG 8x16	BG 12x40	FJ 154	FJ074	FJ045
Moisture %	5.0 max	5.0 max	5.0 max	5.0 max	5.0 max	5.0 max	5.0 max	5.0 max	5.0 max	5.0 max	5.0 max	5.0 max	5.0 max	5.0 max
Hardness %	90 min	90 min	90 min	90 min	90 min	90 min	90 min	90 min	90 min	90 min	90 min			
Apparent density g/L	450 - 550	450 - 550	450 - 550	420 - 530	420 - 530	420 - 530	380 - 500	350 - 450	350 - 450	350 - 450	350 - 450			
Iodine number mg/g	850 - 1100	850 - 1100	850 - 1100	850 - 1100	900 - 1100	900 - 1100	900 - 1100	950 - 1150	950 - 1150	950 - 1150	950 - 1150	800 - 1050	800 - 1050	800 - 1050
Methyl blue mg/g	150 min	150 min	150 min	150 min	150 min	150 min	150 min	150 min	150 min	150 min	150 min	200	100 - 200	100 - 200
Ash %	5 - 18	5 - 18	5 - 18	5 - 18	5 - 18	5 - 18	5 - 18	5 - 18	5 - 18	5 - 18	5 - 18	5 - 18	5 - 18	5 - 18
Particle size mm	3.0	2.5	1.5	2.0	2.5 - 1.25	2.5 - 0.6	1.6 - 0.45	4.75 - 2.5	2.5 - 0.6	2.5 - 1.2	1.6 - 0.45	0.154	0.074	0.045

Package: Packed in big jumbo bags or 25kg bags. Other packaging upon your request is available

Standards: All the above test methods are performed using ASTM protocol for activated carbon.